

# CS18 SOLDERING IRON

- Ergonomic handle
- Iron plated, nickel coated bit for long life
- Upto 30,000 operations tip life
- 9 replacement tips in range
- Choice of Burnproof Silicone cable or standard pvc cable
- Voltages from 12 - 230VAC available



Replacement Bits - 1100 series



Replacement Element



Safety Stand ST6A

## SPECIFICATIONS

Voltage	230, 115, 24, 12
Temperature	390°C
Power	18W
Leakage current	1.5 $\mu$ A
Fitted bit	1100 (2.3mm)
Cable types	PVC or Silicone
Cable Length	1.5 mtr
Plug	UK, EU, USA
Dims (Tip to handle)	182mm

- Manufactured to Din EN 60335-2-45
- CE & EMC Low Voltage directive conformity
- Thermally balanced
- Easy change shimmed bits