

Technical data sheet

Article number:
111-07001

FNT1635BK

Product Group	FastNTube
Material	Polyamide 6.6, UV-resistant (PA66W)
Colour	Black (BK)
Bundle Ø max.	35 mm
Bundle Ø min.	16 mm
Flammability	UL 94 HB
Halogen-free	Yes
Length (L)	175.5 mm
Min.Tensile Strength	320 N
Operating Temperature	-40 °C to +85 °C, (+105 °C, 500 h)
Package Content packed in	box
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	No
Toothing (Serration)	Inside Serrated
Variant	Inside Serrated
Weight/Unit	0.0036 kg
Width (W)	7.5 mm

