



Sample photo

**Order symbol:** CAB P 403017  
**Product nbr:** 8104304  
**Description:** Polyester cabinet  
**Remarks:** Grey door

**EAN:** 6418074050014  
**El. number:**  
 Finland 3424135  
 Denmark 8212018015  
 Sweden 2539819

**Including:** Cabinet base, door with PUR gasket, 3mm double bit lock(s) with transport and plastic key, screws for mounting plate/DIN-rail and wall fastening lugs with screws. Wall mounting screws not supplied.

Dimensions:	L	W	H
mm:	400	300	170
inch:	15.7	11.8	6.7

Materials:	
<b>Material:</b>	GRP
<b>Base colour:</b>	RAL 7032
<b>Cover colour:</b>	RAL 7032
<b>Cover screws material:</b>	Stainless steel
<b>Gasket material:</b>	Polyurethane

Temperatures:	
<b>Short term:</b>	-50 ... 150 °C
<b>Continuous:</b>	-40 ... 70 °C
<b>Short term:</b>	-60 ... 302 °F
<b>Continuous:</b>	-40 ... 158 °F

Accessories:	
MP 4030	Mounting plate

Rating:
<b>Ingress Protection (EN 60529):</b> IP 66
<b>Impact Resistance (EN 50102):</b> IK 10
<b>Electrical insulation:</b> Totally insulated
<b>UV resistance:</b> UL 508
<b>Flammability Rating (UL 746 C 5):</b> UL 94 5V
<b>Glow Wire Test (IEC 695-2-1) °C:</b> 960
<b>UL Type:</b> UL TYPE 3, 3R, 3S, 4, 4X, 12, 13

**Certificates:**

