



Main

Range	Mini Pragma
Range of product	Mini Pragma
Product or component type	Front face
Type of front plate	Plain
Accessory / separate part category	Installation accessory

Complementary

Enclosure mounting	Flush
Type of front cover	Plain
Number of horizontal rows	2
Number of 18 mm modules per row	12
Total number of 18 mm modules	24
Enclosure material	Door: technoplastic Front face: technoplastic
Width	294 mm outside:
Height	377 mm outside:
Depth	18 mm outside:
Colour	Front face: white (RAL 9003)

Environment

Standards	IEC 60695-2-11 IEC 529 EN 50102
Fire resistance	Door: 650 °C Front face: 650 °C
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	806 g
Package 1 Height	5 cm
Package 1 width	29.4 cm
Package 1 Length	37.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	9 kg
Package 2 Height	53.5 cm
Package 2 width	41 cm
Package 2 Length	30.5 cm
Unit Type of Package 3	P12
Number of Units in Package 3	160
Package 3 Weight	156 kg
Package 3 Height	118 cm
Package 3 width	80 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------