

**IN 32 22****Screwdriver bit socket 3/4"**

for in-hex screws, long pattern

Code	ETIM
<b>6276150</b>	<b>EC002157</b>
EAN	UNSPSC
<b>4010886627617</b>	<b>27-11-17-01</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-04-02</b>
Customs tariff number	
82079030	

**20** **3/4"****Article description**

- Acc. to DIN 7422
- Square drive as per DIN 3120 - D 20, ISO 1174, with locking pin
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated

**Article information**

Contents [Qty of pieces]	1	Drive connector square female 3/4" [inch]	
Net weight [kg]	0,482 kg	Standard	DIN 7422 DIN 3120 - D 20 ISO 1174
Total length [mm]	80 mm	Width across flats 1 [mm]	22
Total width [mm]	38 mm	Backup	Locking pin
Surface	chrome-plated	Tip length	25,5 mm
Material	Chrome-vanadium steel	Insert Ø Actuator	38 mm
Drive connector square female (metric)	20,0 mm		