



Part Number : [191150007](#)


Product Description : Avikrimp Snap Spade
Terminal for 22-18 AWG Wire

Series Number : 19115

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : AA-8704-05



Documents & Resources

Drawings

[191150007_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19115
Description	Avikrimp Snap Spade Terminal for 22-18 AWG Wire
Keyword	Spade Terminal, Spade Terminals
Product Name	Avikrimp
Type	Spade Snap
UPC	800753091832

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	0.730/g
Packaging Type	Bag
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm

Stud Size	5 (M3)
Wire Insulation Diameter	3.60mm max.
Wire Size (AWG)	18, 20, 22

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050100</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160036</u>