

Features

- Lightweight and flexible
- European Standard ISO 3821 / EN 559:2003
- Orange colour
- 25m length

RS PRO Hose Pipe

RS Stock No.: 486-570, 486-580, 486-586



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Flexible, smooth, orange hose for liquefied petroleum gas (LPG), propane/butane. Manufactured following the new EN ISO 3821 and EN559 European Norm. The hose is primarily for use in industrial welding and cutting applications.

General Specification

Brand	RS PRO
Features	Flexible
Materials	EPDM, NBR
Colour	Orange
Length	25m
Suitable Applications	Welding
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-30°C
Maximum Working Pressure	20 bar
Hose Pipe Action	Transfer
Standards Met	ISO 3821 / EN 559:2003
Bend Radius	100mm

Products in series

Stock No.	Lenght	Inner Diameter	Outer Diameter	Colour
486-570	25m	6,3mm	13,3mm	Orange
486-580	25m	8mm	14,6mm	Orange
486-586	25m	10mm	17mm	Orange

Similar Products

Stock No.	Lenght	Inner Diameter	Outer Diameter	Colour
486-473	25m	6,3mm	13,3mm	Blue
486-479	25m	8mm	14,6mm	Blue
486-489	25m	10mm	17mm	Blue
486-518	25m	6,3mm	13,3mm	Red
486-502	25m	8mm	14,6mm	Red
486-463	25mm	10mm	17mm	Red