


































MARQUARDT

SERIES 1065 - MICRO-SIGNAL SWITCHES

TO 100 mA 30 V DC

	100 mA 30 V DC 200E3	Terminal type	Terminal description	Operating force in N	Switching point NCC (OP NC) in mm	Minimum OFF range in mm	Switching point (OP NO) in mm	Rest position (FP) max. in mm	Permissible end position (TP) in mm	Actuator description Lever drawing	Miscellaneous	Stock version
Normally open contact (SPNO)												
1068.0541	●		300 long	1 ±0.4			8.95 ±0.3	10.15	6.85		pin right 5 long	
Changeover switch (SPDT momentary)												
1065.0503	●			1 ±0.4	9.45 ±0.3		8.95 ±0.3	10.15	6.85		pin both sides 5 long	●
1065.0603	●			1 ±0.4	9.45 ±0.3		8.95 ±0.3	10.15	6.85		pin both sides 2.5 long	
1065.2000	●		coded cranked	1 ±0.4	13.8 ±0.3		13.3 ±0.3	14.5	11.2		without pin	●
1065.3603	●			1 ±0.4	9.45 ±0.3		8.95 ±0.3	10.15	6.85		pin both sides 2.5 long	
1065.3653	●			1 ±0.4	9.45 ±0.3		8.95 ±0.3	10.15	6.85		pin both sides 2.5 long	
1065.5000	●			≤ 2.2	9.65 ±0.45		9.15 ±0.45	11.35	7.35		pin both sides 5 long	
1065.5103	●			≤ 2.2	12.75 ±0.65		12.05 ±0.65	14.7	9		pin both sides 2.5 long	●
1065.7100	●		coded cranked	≤ 2.2	17.1 ±0.65		16.4 ±0.65	19.05	13.35		without pin	●
1068.0503	●		300 long	1 ±0.4	9.45 ±0.3		8.95 ±0.3	10.15	6.85		pin both sides 5 long	●
1068.0601	●		300 long	1 ±0.4	9.45 ±0.3		8.95 ±0.3	10.15	6.85		pin right 2.5 long	
Changeover switch with OFF position in the center (SPDT momentary - Center OFF)												
1075.0603	●			1 ±0.4	9.45 ±0.3	8.3 - 9.15	8 ±0.3	10.15	6.85		pin both sides 2.5 long	●
1075.2000	●		coded cranked	1 ±0.4	13.8 ±0.3	12.65 - 13.5	12.35 ±0.3	14.5	11.2		without pin	●
1075.3603	●			1 ±0.4	9.45 ±0.3	8.3 - 9.15	8 ±0.3	10.15	6.85		pin right 2.5 long	
1075.3653	●			1 ±0.4	9.45 ±0.3	8.3 - 9.15	8 ±0.3	10.15	6.85		pin left 2.5 long	
Changeover switch (SPDT momentary) can be diagnosed												
1060.2601	●			1 ±0.4	9.45 ±0.3		8.95 ±0.3	10.15	6.85		pin right 2.5 long with resistance circuit	