



Properties	Typical Value	Test Method
Thickness*	0.35" (0.009 m)	
Color*	Gray	
Resistances Surface to Ground (Rtg) Surface to Surface (Rtt)	1 x 10 ⁸ to < 1 x 10 ¹¹ ohms 1 x 10 ⁸ to < 1 x 10 ¹¹ ohms	ANSI/ESD S4.1 & ESD TR53 ANSI/ESD S4.1 & ESD TR53
Tolerance	Width ± 0.250" Length ± 0.250"	

*Color, texture and thickness may very between lots and mills.

The Anti-Fatigue Mat is designed to provide comfort for personnel that must stand or walk for long periods. Constructed with a soft, light weight vinyl these anti-fatigue mats provide easy set-up.

Floor Mat Kit Item Numbers

Size	Gray
24" x 36" (0.6 m x 0.9 m)	AFM2436L1VGR-F
36" x 60" (0.9 m x 18.2 m)	AFM3660L1VGR-F

Mat Kit Includes:

1 Mat, size as specified 1 <u>770115</u> 15' (4.6 m) Floor Ground Cord

Floor Roll Item Numbers

Size	Gray		
3' x 60' (0.9 m x 18.2 m)	AFM36720L1VGR		
(0.9 m x 18.2 m)			

Includes roll of matting material.

Specifications and procedures subject to change without notice.	VINYL, DISSIPATIVE, ANTI-FATIGUE MAT		
SCS	926 JR Industrial Drive, Sanford, NC 27332	DRAWING	DATE
	WEB SITE: <u>StaticControl.com</u>	NUMBER	September
	PHONE: EAST (919) 718-0000 WEST: (909) 627-9634	AFM Series	2020

© 2020 DESCO INDUSTRIES INC Employee Owned