



- **Soul:**
Tinned Copper - stranded 5/10th - 6/10th - 9/10th
- **insulation:**
PVC 85 ° C

Color code: 2 son: white / red - white / blue - white / black - white / yellow - white / green - black / yellow - blue / red - blue / yellow

4 son: white / blue / red / yellow
other colors : Consult us

PRODUCT INFORMATION

Application

These rigid jumpers 5/10th, 6/10th and 9/10th are used for wiring of electronic modules.

Description Cable

assembly: twisted pairs or quads

electrical properties

Operating voltage: **100 V**

Test voltage: **1000 V**

products references

Characteristics



No flame propagation according to:
IEC 60332-1 or NF C 32-070 Cat C2





Operating temperature :
- 25 ° C + 85 ° C



Radius of curvature :
4 x Ø



RoHS Directive

		Thickness Avg. insulation (mm)	Thickness min. insulation (mm)	Outside Diameter. name. conductors (Mm)
JAR 2.05	2 x 5 / 10th	0.25	0,125	1.0
JAR 2.06	2 x 6 / 10ths	0.25	0,125	1.1
JAR 2.09	2 x 9 / 10e	0.25	0,125	1.4
JAR 4.05	4 x 5 / 10th	0.25	0,125	1.0
JAR 4.06	4 x 6 / 10ths	0.25	0,125	1.1