

Features

- Super bright 1300 lumen floodlight
- Ultra-strong housing
- Rotating magnetic hanging hook on the back
- Easy to operate dual switches.
- USB-C rechargeable

RS PRO LED Inspection Lamp, 1300 lm, IP54

RS Stock No.: 0143257



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO LED Inspection Torch, 1300 Lumens, Rechargeable

1300 Lumen white Samsung SMD LEDs
Additional 250 Lumen torch in the head
Ultra strength aluminium & polycarbonate housing
USB Type-C 5V 1A charging - 1m cable included
Red-to-Green charging indicator
Charge time 4 hours
Rotating hanging hook with strong magnets on back
Multi positional fold out stand or hook
IPX4 water resistant
Impact resistant to 1m

General Specifications

Lamp Type	LED
Luminosity	1300 lm
Length	190 mm
Mains Plug Type	USB
IP Rating	IP54
Rechargeable	Yes

Mechanical Specifications

USB	Type-C 5V 1A charging
Battery Charge Time	4 hours
Cable	1m charging cable included
Battery	3.7v 5000mAh Li-ion battery
Dimensions	205 x 57.5 x 42mm
Weight	341g
Operation	<p>TOP SWITCH - Press to activate top torch Sequence: HIGH - 250LM - 7.5hrs > MID - 125LM - 15hrs > LOW - 65LM - 30hrs > OFF</p> <p>LOWER SWITCH - Press to activate main flood Sequence: HIGH - 1300LM - 2.5hrs > MID - 600LM - 5hrs > LOW - 275LM - 10hrs > OFF</p> <p>If left in any mode for over 3 seconds, the next press will turn off.</p>

Approvals

Declarations	EMC RoHS REACH
Standards Met	EN IEC 55015:2019+A11:2020 EN 61547:2009 EN 61000-3-2:2019 EN 61000-3-3:2013+A1:2019 IEC 62321 IP54 IEC 62133

Similar Products

Stock No.	Brand	Product Name	Luminosity	Rechargeable	Mains Plug
0143263	RS PRO	LED Inspection Lamp	1000 lm	Yes	USB
0143257	RS PRO	LED Inspection Lamp	1300 lm	Yes	USB
111-7927	RS PRO	LED Inspection Lamp	White 5700K	Yes	Type C - Europlug
111-7926	RS PRO	LED Inspection Lamp	White 5700K	Yes	Type G - British BS1363
183-5235	RS PRO	LED Inspection Lamp		Yes	USB
186-4628	RS PRO	LED Inspection Lamp	700 lm	Yes	USB
186-4626	RS PRO	LED Inspection Lamp	400 lm	Yes	USB
255-4202	RS PRO	LED Inspection Lamp	720 lm	Yes	USB
186-4627	RS PRO	LED Inspection Lamp	300 lm	Yes	USB
171-8488	RS PRO	LED Inspection Lamp	300 lm	Yes	Type G - British BS1363, USB