

## Datasheet

RS Stock No: 126-1729



### SPECIFICATIONS

#### CAMERA

- Image Sensor: 1/4" CMOS
- Probe Diameter: 9mm
- Probe Length: 300mm
- SideView Camera
- Visual Angle: 55°
- Light Source: 2 white LEDs
- Protection IP67
- Video Output
- Supply: rechargeable built-in Lithium battery

#### MONITOR

- Display: 3,5" colors TFT-LCD Wireless
- Resolution: 640\*480 pixels
- Wireless connecting
- Video and photo recording on SD card
- Photo and video transfer from/to PC through USB port and connecting cable
- Video Output A/V
- Supply: rechargeable built-in Lithium battery

#### APPLICATIONS

- Internal crack control
- Serial number inside the equipment reading
- Lost objects recovery
- Pipes and walls cavity internal control
- Equipment internal inspection
- Pipes and cables location
- Connectors and power sockets check
- Inspection and quality control
- Insulation control
- Internal engine inspection

#### INCLUDED IN THE PACK

- Aluminum carrying case
- 9 mm rigid probe
- Monitor 3,5"
- Mini USB Cable
- Video Cable
- Magnetic monitor mount
- 5V power supply
- Instructions