



ENGLISH

Datasheet

Stock No: 403-409

RS Pro D-sub Interface Module



Product Details

D Subminiature

Screw terminal interface modules with connectors suitable for interfacing electrical cabling to I/O cards and electronic equipment. Designed to mount on standard BS 5584:1978 'DIN' rail. Orange polyamide 6.6 housings with gold plated connector contacts

Temperature range -20 to +50°C

Height 62mm, Width 70mm

Length: 9-way (45mm), 15-way (65mm), 25-way (90mm), 37-way (110mm)

Suitable CSA: (Flexible)2.5mm², (Solid)4 mm²

Interface Modules (DIN Rail Mounting)



ENGLISH

Specifications:

Gender	Male
Number of Contacts	37
Connector Type	D-sub
Mounting Type	DIN Rail Mount
Voltage Rating	50 V
Current Rating	1A
Cable CSA	4mm ²
Dimensions	110 x 70 x 62mm
Depth	62mm
Length	110mm
Width	70mm
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+50°C