CES-B24-WRG-BK - Flat gasket

0801727

https://www.phoenixcontact.com/in/products/0801727

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat gasket made of NBR, size B24



Commercial data


Item number	0801727
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7CZX
GTIN	4046356675260
Weight per piece (including packing)	13 g
Weight per piece (excluding packing)	3.24 g
Customs tariff number	40169300
Country of origin	DE

Technical data

Product properties

Product type	Seal
Type	B24

Dimensions

Dimensional drawing	
Width	57.5 mm
Height	2.5 mm
Length	147 mm
Drill hole distance, horizontal	130 mm
Drill hole distance, vertical	32 mm
Hole diameter	4.5 mm

Material specifications

Seal material	NBR

Environmental and real-life conditions

Ambient conditions


Ambient temperature (operation)	-20 °C ... 80 °C (static)

Mounting

Assembly note	For IP54 degree of protection. For mounting between sealing frame and mounting panel.

Drawings

Dimensional drawing



Dimensional drawing

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/in/products/0801727

DNV
Approval ID: TAE00003VJ

Classifications

ECLASS

ECLASS-13.0	23071590
ECLASS-15.0	27440292

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	31401600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.582 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in