

/ RUN-R //



**100 %
metal
free**



RUN-R 400 HIGH

Art. Nr.: 62613

EN ISO 20345: 2011 - S3 SRC

Sizes: 37 - 48

APPLICATIONS //

metal free model for trades men, industry, warehousing and logistics, manufacturing, public services, humid environments

TECHNICAL SPECIFICATIONS //

sole: PU2D | very lightweight | highly flexible | excellent shock absorption | excellent levels of grip (SRC) | oil, hydrocarbon & chemical-resistant | grooves at the back of the heel for a better grip when the heel first touches the ground & deep grooves for better grip in the forefoot area | pronounced heel & GRIPSTEP profile for ladders and stairs

upper: water-resistant embossed full-grain leather

lining: 3D polyester mesh

toe cap: metal free

penetration-resistant midsole: metal free

hygienic insole: removable | anatomically shaped with shock absorbers in the heel & forefoot | microfibre top layer for better abrasion resistance & durability | very high moisture absorption capacity & fast drying bottom layer made from 90% recycled PU foam | washable at 30°C enhances hygiene

weight: 570 g in size 42