

Technical data sheet

Article number:
111-08280

T80I



Product Group	Cable Ties for temperatures up to + 105°C (heat stabilised)
Product Family	T-Series in PA66HS black
Material	Polyamide 6.6, heat stabilised (PA66HS)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	85.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Halogen-free	Yes
Length (L)	305 mm
Min.Tensile Strength	355 N
Operating Temperature	-40 °C to +105 °C
Package Content packed in	pack
Pack Cont.	1000 pcs.
Releasable Closure (Yes/No)	No
Thickness (T)	1.3 mm
Toothing (Serration)	Inside Serrated
UV-resistant acc. to ASTM D6779 (Yes/No)	No
Variant	Inside Serrated
Weight/Unit	0.002065 kg
Width (W)	4.7 mm

