

## FEATURES

- Glass cartridge
- 5mm x 20mm cartridge size
- T Speed Rating
- Anti-surge
- Low Breaking Capacity

## RS PRO, 3.15A Glass Cartridge Fuse, 5 x 20mm, Speed T

RS Stock No.: 563-621



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Glass cartridge fuses are ideal for providing protection to devices or internal circuits from short circuits and overcurrent. They are deliberately weaker components which, when too much current is drawn, will blow. Once the fuse has blown it will need replacing in order to make the circuit complete and allow the flow of current.

## General Specifications

<b>Fuse Speed</b>	T
<b>Body Material</b>	Glass
<b>Application Category</b>	GRL
<b>Includes Indicator</b>	No
<b>Size Designation</b>	Miniature
<b>Applications</b>	Industrial, Commercial, Home/Residential, Automotive

## Electrical Specifications

<b>Current Rating</b>	3.15A
<b>Voltage Rating</b>	250V ac
<b>High Rupture Capacity</b>	No
<b>Breaking Capacity (at Maximum Voltage Rating)</b>	35A
<b>Resistance</b>	0.0187Ω

## Mechanical Specifications

<b>Fuse Size</b>	5mm x 20mm
<b>Overall Length</b>	20mm
<b>Diameter</b>	5.2mm
<b>Overall Dimensions</b>	5.2mm x 20 mm

## Operation Environment Specifications

<b>Maximum Operating Temperature</b>	125°C
<b>Minimum Operating Temperature</b>	-55°C

## Approvals

<b>Compliance/Certifications</b>	CSA Acceptance, UL Recognised, RoHS Compliant, CCC, UTE, PSE, KTL, CQC, TUV, VDE, BSI, SEMKO Approved
----------------------------------	---



S