



Main

| | |
|------------------------------|-----------------------------|
| Device short name | MN |
| Product or component type | Voltage release |
| Device application | Control |
| Range compatibility | PowerPact B Compact NSXm |
| Voltage release type | Undervoltage release |
| [Uc] control circuit voltage | 440...480 V AC |

Complementary

| | |
|-------------------------------|--|
| Threshold tripping voltage | 0.35...0.7 x Un - during opening time 0.85 x Un - during closing time |
| Mounting mode | Clip-on |
| Response time | < 50 ms |
| Auxiliary connection terminal | Pre-wired 0...0.8 mm ² (AWG 18) stranded copper |
| Wire stripping length | 8 mm |
| Cable length | 1 m |

Offer Sustainability

| | |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 1649 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications