



Multi Purpose



Light Duty

Our best Multi-purpose Gloves, now made green

- **Everyday usability:** HyFlex® 11-800 industrial gloves' nitrile foam coating makes them exceptionally breathable, for less irritable daily use
- **Elevated comfort:** ZONZ™ Comfort Fit Technology optimized lining relieves tension, for PPE gloves with peerless comfort
- **Certified skin-friendliness:** These HyFlex® gloves are also Dermatest®-certified for skin-friendliness
- **Guaranteed cleanliness:** In addition, they benefit from a proprietary washing process that removes impurities
- **Enhanced grip:** Beyond comfort, Hyflex® 11-800 industrial working gloves' nitrile foam coating delivers better grip in both dry and slightly oily conditions
- **Improved durability:** They boast ANSI/ISEA and EN compliant abrasion resistance, for lasting wear
- **Sustainable design:** HyFlex® 11-800 sustainable Multi-Purpose gloves are designed with 47% recycled content* reducing our carbon footprint by 153g CO2eq/pair** and plastic-free inner packaging that contains 70% fewer materials^



*% is the minimum recycled content in final product

** vs standard nylon Multi-Purpose glove

^vs previous technology version

Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Picking, fastening components
- Adjusting systems and screwing
- Loading and unloading trucks and vehicles
- Handling incoming goods
- Product shipping, transport and delivery
- Lock smith

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-800

The Multi-Purpose standard for 20 years, now designed to be even more comfortable

Key Features

- **Breathable nitrile coating:** Safety gloves that ensure all-day comfort
- **ZONZ™ Comfort Fit Technology:** For PPE gloves with a tailored feel
- **Dermatest® certification:** Skin-friendliness guaranteed
- **Glove made with 47% recycled content*:** Carbon footprint reduction of 153g CO2eq/pair**

*% is the minimum recycled content in final product

** vs standard nylon Multi-Purpose glove

Technologies



DMF free



ZONZ™

Comfort Fit Technology

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



EN 407



dermatest-guarantee.de



STANDARD 100

1408033
Centexbel

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-800	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon Cuff Style: Knitwrist	15	6, 7, 8, 9, 10, 11	212-262 mm/8.34-10.31 inches	Grey	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell