



6993 - POLYMER RUN TEE MALE BSPP FDA NICKEL PLD EPDM SEAL



maximum working pressure	16 bar 2 MPa 232 psi
working temperature	-10 to 95 °C 14 to 203 °F 263 to 368 °K
vacuum capability	755 mm Hg
body	BIO-BASED POLYMER
sub-base	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	EPDM
gripping ring	STAINLESS STEEL

Part Nb	ØD (MM)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	H1 (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
6993 04 10	4	G1/8	5	13	8.5	30	18	14.5	.009
6993 04 13	4	G1/4	5.5	16	8.5	30	18	14.5	.014
6993 04 19	4	M5x0,8	3.5	8	8.5	32	19	14.5	.006
6993 06 13	6	G1/4	5.5	16	10.5	38	22	17.5	.016
6993 06 19	6	M5x0,8	3.5	10	10.5	39	23	17.5	.009
6993 08 10	8	G1/8	4.5	13	13.5	54	31	23	.019
6993 08 17	8	G3/8	5.5	20	13.5	52	29	23	.03
6993 10 17	10	G3/8	5.5	20	16	61	35	26.5	.055
6993 10 21	10	G1/2	7.5	24	16	61	35	26.5	.051
6993 12 17	12	G3/8	5.5	20	19	67	36	31	.042