


quick exhaust valve SEU-3/8-NPT

Part number: 9800

FESTO

With built-in silencer.

The exhaust noise level is measured at 6 bar to atmosphere at 1 m distance.



Data sheet

Feature	Value
Valve function	Quick exhaust
Pneumatic connection, port 1	3/8 NPT
Pneumatic connection, port 2	3/8 NPT
Mounting type	Threaded
Standard nominal flow rate, exhaust	2,280 l/min
Standard flow rate for exhaust 6->0 bar	4,680 l/min
Standard nominal flow rate for pressurisation 6->5 bar	2,880 l/min
Operating pressure	0.2 ... 10 bar
Ambient temperature	-20 ... 75 °C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Nominal size	11 mm
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Medium temperature	-20 ... 75 °C
Sound pressure level	83 dB(A)
Materials note	Conforms to RoHS