



Part Number : [1300190003](#)

Product Description : Die Block 2 Pole Shorting Plug with 0.305m (1.0') Chain, Yellow

Series Number : 130019

Status : Active

Product Category : Circular Industrial Connectors

Engineering Number : 22803



Documents & Resources

Drawings

[1300190003_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[UKCA - Declaration of Conformity](#)

[CE - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130019
Description	Die Block 2 Pole Shorting Plug with 0.305m (1.0') Chain, Yellow
IP Rating	N/A
Product Name	Die Block
Type	Die Block
UPC	78678822803

Agency

CSA	LR6837
UL	E46237

Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V AC

Physical

Coupling Type	Push to Lock
Gender	Male
Keyway	None
Length	N/A
Material - Component	Nitrile/PVC
Mounting Thread Size	N/A
Net Weight	274.423/g
Orientation	N/A

Panel Mount	N/A
Poles	2
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

This document was generated on Nov 05, 2025