

# M18 FUEL Powered Fish Tape Base

M18 FPFT-0

- Power to Pull 60m through 360° Bends - Completes the Toughest Runs
- Compatible with 3 Interchangeable Replacement Cartridges up to 72m Steel & 30m Non-Conductive
- AUTO-RUN Powered Feed & Retract - Less Muscle Effort, Reduced User Fatigue

MODEL VARIANT



## INCLUDES

- M18 FPFT-0 (1)

**Categories:** Plumbing

## Range Spec



M18 FPFT-0

### WHAT'S INCLUDED

| |
|---|
| M18 FPFT-0 (1) |

| PRODUCT SPECIFICATIONS | |
|---|---|
| Weight without battery pack (kg) | 3.1 |
| Weight with battery pack if applicable (kg) | With 2.0Ah : 3.5 ; With 12.0Ah : 4.6 |
| Recommended Ambient Operating Temperature | '-18°C to +50°C |