

D 21 46

Socket 1"

Bi-hexagon UD profile

Code	ETIM
6175120	EC002203
EAN	UNSPSC
4010886617519	27-11-17-04
Country of origin	eCl@ss
Germany	21-04-02-19
Customs tariff number	
82042000	



Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - D 25, ISO 1174, with locking pin
- Manually operated, with non-slip cross knurling
- GEDORE vanadium steel 31CrV3, chromed
- * not standardised

Article information

Contents (Qty of pieces)	1	Standard	DIN 3124 ISO 1174 DIN 3120 - D 25 ISO 2725-1
Net weight [kg]	0,842 kg	Width across flats 1 [mm]	46
Total length [mm]	75 mm	Backup	Locking pin
Total width [mm]	66,4 mm	Insert-Ø 1	66,4 mm
Surface	chrome-plated	Working length	75,0 mm
Material	Chrome-vanadium steel 31CrV3	Insert-Ø 2	50,0 mm
Drive connector square female (metric)	25,0 mm	Operating depth	33,5 mm
Drive connector square female 1" [inch]			