

#### **FEATURES**

- Extremely flexible
- Lightweight and user-friendly
- Excellent kinkresistance
- RoHS compliant
- Good abrasion resistance
- Silicone-free

## RS PRO PVC Flexible Tubing, Blue, 17mm External Diameter, 30m Long, Reinforced, 55mm Bend Radius, Compressed Air, Water

RS Stock No.: 293-2101



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

A high quality, exceptionally flexible PVC hose borne out of technical innovation and superior quality materials that is ideal for industrial use. Lightweight, its ergonomic design reduces operator fatigue and associated strains, helping to improve overall productivity without compromising on performance and durability.

#### **General Specifications**

Material	PVC
Colour	Blue
Reinforced	Yes
Material Softness	No
Application	Compressed Air, Water

#### **Mechanical Specifications**

Inner Diameter	12mm
Outer Diameter	17mm
Length	30m
Bend Radius	55mm
Safety Factor	3:1



#### **Operation Environment Specifications**

Minimum Operating Temperature	-15°C
Maximum Operating Temperature	60°C
Maximum Working Pressure	11bar

#### **Approvals**


Compliance/Certifications	RoHS Certificate Of Compliance

#### MULTI-PURPOSE REINFORCED PVC HOSE

(U.K. And European Sizes)

Product Ref	Size		Weight per cail	Working Pressure		Bend Radius
	1.0.	0.D.	Kgs	BAR	PSI	mm
CX 6	6	10.5	1.8	18	260	28
CX 8	8	12.5	2.6	15	220	29
CX 10	10	14	2.9	13	190	40
CX 12	12	17	3.8	11	160	55
CX 16	18	21	6.7	11	160	95
CX 19	19	24	7.8	-11	160	135

# CX RANGE Pressure/Temperature Relationships



Max. recommended continuous working temperature = 60°C

### Flexible Tubes

