

Professionally approved products.

Datasheet

DC Geared Motor, 12 V dc, 20 Ncm, 136 rpm, 2.9 W

RS Stock number 2559598



Features

38mm Ironless 12/24Vdc Motor and Spur Gearbox

The reversible motor has an ironless rotor giving linear speed-torque performance

The commutation system uses precious metal brushes for high efficiency and sensitivity to suit servo application and general-purpose requirements

The gearbox construction employs a fibre wheel first stage followed by steel gears on bronze shafts

Output drive shaft has a flat machined on to simplify load coupling