

Product information

ORBITAL ACTION JIGSAW



Satisfying the professional's needs

4350FCT

Max in steel	10 mm
Max in wood	135 mm
Strokes per Minute	800-2800 spm
Stroke Length	26 mm
Noise sound pressure	84 dB(A)
Noise sound power	95 dB(A)
Noise K factor	3 dB(A)
Input wattage	720 w
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	8 m/sec ²
Vibration: Cutting Sheet Metal	4.5 m/sec ²
Net weight	2.4 kg



STANDARD EQUIPMENT: Assorted blades, Hex wrench, Anti splintering device, Cover plate, Dust nozzle, Carry case

- Quick release tool-less blade change
- Sturdy adjustable base for accurate cutting
- Variable electronic speed control
- Built-in job light

Details correct as of: 30-8-2017

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com