



Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Wave solder capable to 265°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1969540-8
HOUSING, PLUG, 8P, DUAL ROW,
EP2.5

Customers Also Bought

TE Part #1241050-4
2x4P MOD II BREAK AWAY HDR,SMD,
BLISTER

TE Part #DT06-6S-EP11
PLG, 6P, BLK, N, SEAL RET, XCAP

TE Part #1473005-1
SEMI HARD TRAY DDR SOCKET 200P

TE Part #160773-6
PL LOOSE PIECE REC 0.5-1.5 MM2
PTPBR

TE Part #5207719-2
FEMALE SCREWLOCK KIT,BULK PKG

TE Part #1-726388-2
187 FASTON,TAB,TPBR

TE Part #353293-6
MINI CT MT REC ASSY 6P GRAY

TE Part #5-103414-1
03 MODII HDR SRST SHRD LF

TE Part #5-104363-1
02 MTE HDR SRST LATCH .100CL

TE Part #5-1622820-0
3520 47R 5%

Documents

Product Drawings

ASSY, HDR, VERT, NO-BOSS, DUAL ROW,EP2.5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1969582-8_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1969582-8_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1969582-8_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[7-1773461-6_EP2.5_Connector_Series](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[VDE Certificate](#)

English