



**ACCESSORIES**

**END FITTINGS 16 Z**

8791 (MM)

**OPEN END FITTING 16 Z**

- For accessing bolts in cramped and hard-to-reach locations, easy to change
- Forged
- Chrome-vanadium steel, matt chrome-plated
- With eject-pin for unlocking



Ø	mm	mm	mm	Depth gauge		Code	No.
16	7	5	20.5	32	0.080	7774470	8791-07
16	8	5	20.5	32	0.080	7774550	8791-08
16	9	5	20.5	32	0.080	7774630	8791-09
16	10	7	29.0	32	0.090	7710070	8791-10
16	11	7	29.0	32	0.090	7710150	8791-11
16	12	7	29.0	32	0.090	7676890	8791-12
16	13	8	34.5	32	0.120	7710230	8791-13
16	14	8	34.5	32	0.120	7710310	8791-14
16	15	8	34.5	32	0.120	7710580	8791-15
16	16	9	41.5	32	0.160	7710660	8791-16
16	17	9	41.5	32	0.160	7710740	8791-17
16	18	9	41.5	32	0.160	7676970	8791-18
16	19	10	45.0	32	0.180	7710820	8791-19
16	20	10	45.0	32	0.180	7710900	8791-20
16	21	10	45.0	32	0.180	7677000	8791-21
16	22	11	56.0	32	0.220	7711040	8791-22
16	23	11	56.0	32	0.220	1977164	8791-23
16	24	11	56.0	32	0.220	7711120	8791-24
16	25	11	56.0	32	0.220	1552279	8791-25
16	26	11	56.0	32	0.220	1552287	8791-26
16	27	12	60.5	32	0.260	7711200	8791-27
16	28	12	68.0	32	0.300	1207008	8791-28
16	29	12	68.0	32	0.300	1552309	8791-29
16	30	12	68.0	32	0.300	7774710	8791-30
16	32	12	68.0	32	0.300	7774980	8791-32
16	36	12	68.0	32	0.300	1552317	8791-36

8754

**RATCHET HEAD 16 Z**

- For accessing bolts in cramped and hard-to-reach locations, easy to change
- Forged
- Chrome-vanadium steel, matt chrome-plated
- With eject pin for unlocking



Ø	Type	"	mm	Depth gauge		Code	No.
16	3/8"	10.0	32	0.170	7711980	8754-01	
16	1/2"	12.5	32	0.270	7712010	8754-02	

Max. continuous load of ratchet according to DIN EN ISO 6789:2003 and/or maximum load of cavity

No. **8754-01** Continuous load 3/8" = 135 N-m

8791 (AF)

**OPEN END FITTING 16 Z**

- For accessing bolts in cramped and hard-to-reach locations, easy to change
- Forged
- Chrome-vanadium steel, matt chrome-plated
- With eject-pin for unlocking



Ø	"AF	mm	mm	Depth gauge		Code	No.
16	1/4	5	20.5	32	0.090	1211421	8791-1/4AF
16	5/16	5	20.5	32	0.080	7720030	8791-5/16AF
16	3/8	7	29.0	32	0.090	1211447	8791-3/8AF
16	7/16	7	29.0	32	0.090	7720110	8791-7/16AF
16	1/2	8	34.5	32	0.090	7720380	8791-1/2AF
16	9/16	8	34.5	32	0.120	7720460	8791-9/16AF
16	5/8	9	41.5	32	0.160	7720540	8791-5/8AF
16	11/16	9	41.5	32	0.160	7720620	8791-11/16AF
16	3/4	10	45.0	32	0.180	7720700	8791-3/4AF
16	13/16	10	45.0	32	0.090	1211439	8791-13/16AF
16	7/8	10	45.0	32	0.220	7720890	8791-7/8AF
16	15/16	11	56.0	32	0.220	7720970	8791-15/16AF
16	1	11	56.0	32	0.220	7721000	8791-1AF
16	1.1/16	12	60.5	32	0.260	7721190	8791-1.1/16AF
16	1.1/8	12	68.0	32	0.300	7721270	8791-1.1/8AF
16	1.3/16	12	68.0	32	0.300	7776170	8791-1.3/16AF
16	1.1/4	12	68.0	32	0.300	7776250	8791-1.1/4AF
16	1.5/16	12	68.0	32	0.300	7776330	8791-1.5/16AF

8790 - 8793

**FIXED SQUARE HEAD 16 Z**

- For accessing bolts in cramped and hard-to-reach locations, easy to change
- Forged
- Chrome-vanadium steel, matt chrome-plated
- With eject pin for unlocking



Ø	Type	"	mm	Depth gauge		Code	No.
16	3/8"	10.0	32	0.350	7709490	8790-00	
16	1/2"	12.5	32	0.380	7709570	8793-00	

Max. continuous load of ratchet according to DIN EN ISO 6789:2003 and/or maximum load of cavity

No. **8790-00** Continuous load 3/8" = 135 N-m  
**8793-00** 1/2" = 340 N-m