

# PSM-SET-B-FOC/4-HCS/PN - FO connectors



2313782

<https://www.phoenixcontact.com/in/products/2313782>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO connectors, degree of protection: IP20, number of positions: 4, MM, material: Plastic, cable outlet: straight



## Your advantages

- Suitable for quick and easy field assembly or repair
- Flexible application, thanks to reusable connector
- Outstanding transmission properties
- Ideal for PCF graded-index (GI) fibers
- Robust design, thanks to B-FOC pin connector pattern
- No bonding or polishing

## Commercial data

Item number	2313782
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABN
Product key	ABNIAB
Catalog page	Page 377 (C-2-2019)
GTIN	4046356573474
Weight per piece (including packing)	24.2 g
Weight per piece (excluding packing)	24.2 g
Customs tariff number	85367000
Country of origin	DE

## Technical data

### Product properties

Product type	Fiber optic connector (cable side)
Number of positions	4
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Attenuation	≥ 2 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

### Dimensions

Length	82 mm
--------	-------

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Plastic

### Cable/line

Cable type	for all common PCF cable types
External cable diameter	2.2 mm ... 2.2 mm
Individual wire diameter	2.2 mm

### FO cable

Number of fibers	4
Fiber type	PCF
Attenuation	≤ 1.5 dB

### Characteristics

Attenuation	≥ 2 dB (Insertion attenuation)
-------------	--------------------------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

# PSM-SET-B-FOC/4-HCS/PN - FO connectors



2313782

<https://www.phoenixcontact.com/in/products/2313782>

## Classifications

### ECLASS

ECLASS-11.0	19170122
ECLASS-12.0	19170122
ECLASS-13.0	19170122

### ETIM

ETIM 9.0	EC001122
----------	----------

### UNSPSC

UNSPSC 21.0	43223300
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

# PSM-SET-B-FOC/4-HCS/PN - FO connectors



2313782

<https://www.phoenixcontact.com/in/products/2313782>

## Mandatory accessories

### PSM-HCS-KONFTOOL/B-FOC - Assembly tool

2708465

<https://www.phoenixcontact.com/in/products/2708465>



HCS assembly kit for B-FOC(ST) quick mounting connectors, including stripping blade, stripping pliers, aramide yarn scissors, fiber stripper, microscope, fiber cleaving tool for standard HCS and HCS GI fibers, four B-FOC(ST) connectors for standard HCS fiber, and documentation

---

## Accessories

### FL FOC PN-B-HCS-200/230 - FO cable

2313766

<https://www.phoenixcontact.com/in/products/2313766>



PROFINET PCF fiber cable, duplex 200  $\mu\text{m}$  / 230  $\mu\text{m}$ , for installation in stationary systems and machines, type B, PVC outer sheath, sold by the meter without plug

# PSM-SET-B-FOC/4-HCS/PN - FO connectors



2313782

<https://www.phoenixcontact.com/in/products/2313782>

## FOC-PN-HCS-1018/IP20/... - FO patch cable

2901556

<https://www.phoenixcontact.com/in/products/2901556>



PCF PROFINET installation cable for assembly (IP20 heads only) for installation in stationary systems and machines, individual elements of polyamide (PA), ozone- and UV-resistant, with PVC outer sheath

---

## PSM-HCS-KONFTOOL/B-FOC - Assembly tool

2708465

<https://www.phoenixcontact.com/in/products/2708465>



HCS assembly kit for B-FOC(ST) quick mounting connectors, including stripping blade, stripping pliers, aramid yarn scissors, fiber stripper, microscope, fiber cleaving tool for standard HCS and HCS GI fibers, four B-FOC(ST) connectors for standard HCS fiber, and documentation

# PSM-SET-B-FOC/4-HCS/PN - FO connectors



2313782

<https://www.phoenixcontact.com/in/products/2313782>

## FOC-ADAPTER:ST/ST-MM - Fiber optic coupling

1208099

<https://www.phoenixcontact.com/in/products/1208099>



Fiber optic coupling, degree of protection: IP20, number of positions: 1, material: Metal, connection method: Coupling, cable outlet: straight, color: silver/matt, Ethernet

---

## FOC-TOOL-FERRULECLEANER-2.50 - FO accessories

1407029

<https://www.phoenixcontact.com/in/products/1407029>



2.50 mm ferrule cleaner, for ST, SC, FC, E2000 (also APC), approx. 500 cleaning cycles

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)