

Metal Circular Saw LXT®

DCS553

18 V • 150 mm • 4 200 min⁻¹

Quick, almost spark-free metal cutting with brushless saw

A circular metal saw with a brushless motor. Equipped with a blade with a 150 mm diameter that can achieve a max. cutting depth of 57.5 mm. Suitable for quick, almost spark-free cutting of metal. An ideal tool for electricians and air-conditioning and roofing fitters.



LXT **BL** **ADT** **BRAKE**

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	4200 min ⁻¹
Max. Cutting Depth at 90°	57,5 mm
Electronic brake	✓
Blade Diameter	150 mm
Bore Size (Arbor Diameter)	20 mm
Sound Power Level (L _{WA})	114 dB(A)
Sound Pressure Level (L _{pA})	106 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Cutting metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting metal	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- Cutting metal quickly and without sparks.
- LED light illuminates the work site
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Electric brake for maximum productivity and increased operator safety
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

164095-8 Parallel Guide		783203-8 Hex Wrench 5 Mm	
821551-8 Makpac case (3)		839751-6 Inner tray (3)	
B-47036 Circular Saw Blade, Specialized, TCT,		B-69325 Circular Saw Blade, Efficut, TCT,	
B-69331 Circular Saw Blade, Efficut T.C.T. 150			

Other

User manual

Parts drawing