



## Technical data

### RNA22/6XLL/3AS

Roller follower without inner ring

#### PRODUCT DEFINITION

<b>Brand</b>	NTN
<b>D - External diameter</b>	19 mm
<b>Fw - Under rollers diameter</b>	10 mm
<b>C - Width of bearing, drawn cup or outer ring</b>	11,8 mm
<b>e - Inlet diameter of roller or washer</b>	16 mm
<b>Bearing with/without cage</b>	Avec
<b>Precision class</b>	P0
<b>Mass</b>	0,018 kg

#### PRODUCT PERFORMANCE

<b>Cr - Dynamic load rating</b>	4550000 mN
<b>C0r - Static load rating</b>	4250000 mN
<b>Track load capacity cylindrical outer ring</b>	4400000 mN
<b>N lim - Grease lubrication limit speed</b>	60000 °/s
<b>Tmin - Min operating temperature</b>	253,15 °K
<b>Tmax - Max operating temperature</b>	373,15 °K



#### NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15