



ENGLISH

INTERCHANGEABLE WALL PLUG POWER SUPPLY 24VDC 40WATT



The RS Pro Range of 40 Watt Interchangeable wall plug power supplies provide 40 Watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro & USA Heads, all Efficiency Level VI and carry worldwide safety approvals.

Features:

- Interchangeable AC Head
- 3 Year Warranty
- Level VI Efficiency
- Worldwide Approvals





ENGLISH

Specification	
RS Stock Number	9032911
Input Voltage Range	90-264Vac
Input Frequency Range	47-63Hz
Input Current Rated	1.0A Max
Input AC Heads	UK, Euro & USA
Output Voltage Rating	+24V
Output Current Range	1.7A
Output Min Current	0.0A
Output Connection Type	2.1x5.5x12mm Centre Positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 5%
Ripple & Noise	<240mVp-p
Efficiency	87.62% Min
Over Voltage Protection	30VDC Maximum
Over Load Protection	≤2.6A Output Load
Operating Temperature	0°C to +40°C
Storage Temperature	-10 to +70°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	UL/CUL, GS, CE(LVD), RCM
EMI Standard	Meet FCC class B, CE, VCCI - II
MTBF	50K Hours
Size mm max.	90 (L) x 38 (W) x 59.4(H)
Weight	200 g
Cable Length	1.2 m
Regulator Type	Switching Power Supply