


PRODUCT PROFILE

edding 2000 C permanent marker



Product text

- Permanent marker for marking and labelling almost all materials, e.g. paper, cardboard, metal, plastic and glass
- The round nib has a stroke width of 1.5-3 mm
- Waterproof and wear-resistant on almost all surfaces
- Available in 10 different colours
- The product is refillable
- Spare nibs are available
- Low-odour ink with no added toluene/xylene
- High-quality aluminium barrel

Target group

- Professionals e.g. in industry, craft, or public health who need markers with outstanding attributes for different materials, surfaces and applications
- Users who need to deliver a professional result
- Users with permanent marking needs in offices or administration rooms
- Users with organisational and structuring tasks around an office desk
- Households with 2+ persons
- Households with organizing, labelling and general marking needs

USPs

- Long lasting marks on a variety of materials with a solid aluminium marker

Benefits for the consumer

- Ready to use
- Cap can be stored on the end of the barrel to prevent risk of losing it
- Broad colour assortment
- High-quality brand product
- Made in Germany

Product Information

Product ingredients

- | | |
|--------------------|----------------------|
| Alcohol based ink | • yes |
| Solvent based ink | • Yes |
| Dye based ink | • yes |
| Excluded additives | • toluene and xylene |

Product features

- | | |
|----------------------|------------|
| Shape of nib | • round |
| Stroke width | • 1,5-3 mm |
| Spare nibs available | • Yes |
| Permanent | • Yes |
| Low-odour | • Yes |
| Waterproof | • Yes |
| Wear-resistant | • yes |
| Smudge-proof | • Yes |
| Lightfast | • yes |
| Quick-drying | • Yes |

Applicable on

- Paper
- Carton/Cardboard
- Rubber
- Plastic
- Glass
- Wood
- Metal/Steel/Iron
- Concrete/Stone
- Ceramic
- Terracotta
- Leather
- Polystyrene
- Foils

Refillable

Refillable with

- Yes
- edding T 25 refill ink
- edding MTK 25 refill ink in colour 001-004
- edding T 100 refill ink in colour 001-004
- Yes
- Yes

Cap can be repositioned

Roll stopp present

- Yes
- Yes

Product material

Material of cap

Material of mouthpiece

Material of barrel

Material of nib

Material of filter

- Polypropylene
- Polypropylene
- Aluminium
- Acrylic
- Polyester

Colour

Number of colours (product)

Colour range of product (colour codes)

Colour range of product (colour names)

- 10
- 001-010
- black
- red
- blue
- green
- yellow
- orange
- brown
- violet
- pink
- light blue
- barrel
- cap
- mouthpiece

Communication of writing colour by

- barrel
- cap
- mouthpiece

	SAP no.	KEA / order no.
Single product	525XXX	4-2000CXXX
Blister of 1	8277XXX	4-2000C-1-1XXX
Blister of 3	8278XXX	4-2000C-3-1XXX
Blister of 4	6540XXX	4-2000C-4-4XXX
Folding box of 10 assorted (001-010)	1101999	-
Set of 4 assorted (001-004)	6537999	4-2000C-4
Folding box of 10 assorted (001-010)	6561999	4-2000C999
Eurohook of 30 assorted (30x 001)	301707000	-

EAN code				
	Single product	Folding box	Outer carton	Shipping carton
001 black	4004764878406	4004764878413	-	4004764878420
002 red	4004764878437	4004764878444	-	4004764878451
003 blue	4004764878611	4004764878628	-	4004764878635
004 green	4004764878468	4004764878475	-	4004764878482

EAN code				
	Single product	Folding box	Outer carton	Shipping carton
005 yellow	4004764950461	4004764950478	-	4004764950485
006 orange	4004764950492	4004764950508	-	4004764950515
007 brown	4004764950522	4004764950539	-	4004764950546
008 violet	4004764950553	4004764950560	-	4004764950577
009 pink	4004764950584	4004764950591	-	4004764950607
010 light blue	4004764950614	4004764950621	-	4004764950638
Blister of 1 001 black	4004764893393	-	4004764893409	4004764893416
Blister of 1 002 red	4004764893805	-	4004764893812	4004764893829
Blister of 1 003 blue	4004764893836	-	4004764893843	4004764893850
Blister of 1 001 black	4004764894468	-	4004764894475	4004764894482
Blister of 3 001 black (3x 001)	4004764880003	-	4004764880010	4004764880027
Blister of 3 002 red (3x 002)	4004764880034	-	4004764880041	4004764880058
Blister of 3 assorted (001-003)	4004764880096	-	4004764880102	4004764880119
Blister of 4 assorted (001-004)	4004764894499	-	4004764894505	4004764894512
Folding box of 10 assorted (001-010)	4004764950645	-	-	4004764950652
Set of 4 assorted (001-004)	4004764879007	-	4004764879014	4004764879021
Folding box of 10 assorted (001-010)	4004764950645	-	-	4004764950652
Eurohook of 30 assorted (30x 001)	4057305022103	-	-	4057305022103

Packaging					
	Net weight	Folding box	Outer carton	Shipping carton	Pallet
Single product	12,8 g	10 pcs	-	600 pcs	19.200 pcs
Blister of 1	12,8 g	-	10 pcs	100 pcs	3.200 pcs
Blister of 3	38,4 g	-	10 pcs	40 pcs	960 pcs
Blister of 4	52,8 g	-	5 pcs	40 pcs	960 pcs
Folding box of 10 assorted (001-010)	130 g	-	-	60 pcs	1.920 pcs
Set of 4 assorted (001-004)	60 g	-	10 pcs	80 pcs	1.920 pcs
Folding box of 10 assorted (001-010)	142 g	-	-	60 pcs	1.920 pcs