



Product data sheet

Power tools for trade & industry

HGS 55/50

INDUSTRIAL HGS 55/50



Straight handle, central drive end

The most important data

Permitted grinding stone diameter	50 mm
No-load speed	18,000 rpm
Rated power, output	150 W

Part Number 0 602 228 234

Technical data

Technical data

Frequency	300 Hz
Voltage	200 V
Permitted grinding stone diameter	50 mm
No-load speed	18,000 rpm
Rated power, input	260 W
Rated power, output	150 W
Rated current	3.2 A
Weight as per EPTA	2 kg
Toolholder, drive end	Collet 6 mm
Switch version	Rocker switch



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

