



4810 - DOUBLE FEMALE, ECONOMY, STAINLESS STEEL BALL VALVE



working temperature	-20 to 150 °C -4 to 302 °F 253 to 423 °K
body	STAINLESS STEEL 316L
retaining nut	STAINLESS STEEL 316L
stem	STAINLESS STEEL 316L
'O'-rings	PTFE
handle	STAINLESS STEEL

Part Nb	C	E (mm)	ØG (mm)	H (mm)	L (mm)	M (mm)	(kg)
	All	All	All	All	All	All	All
4810 08 13	G1/4	10	30	44.5	53.5	110.5	.206
4810 10 17	G3/8	10	30	44.5	53.5	110.5	.19
4810 15 21	G1/2	13	32.5	47	60	110.5	.245
4810 20 27	G3/4	14	40	54.5	70	131.5	.418
4810 25 34	G1	17	49	58.5	79	131.5	.648