

415CO/SP19A
Twist drills with cylindrical shanks, HSS-CO 5%
DIN 338

For drilling holes into STAINLESS steel,
 alloy steel, cast iron,
 mild steel, light alloys.

∅ 1÷10 x 0.5 mm

 560 g

 115x170x40 mm



	art.	
004150440	415CO/SP19A	∅ 1÷10 x 0,5 mm