

LEDXSSBRBN

Pan & Tilt Bracket Coastal Grade – Black

Features & Benefits

- Polycarbonate mounting base
- 316 stainless steel bracket and screws
- Easy quick fit bracket installation
- For use with models: LEDX10FLBN, LEDX10PIRBN, LEDX20FLBN, LEDX20PIRBN, LEDX30FLBN, LEDX30PIRBN



Technical Data

Installation Type	Stirrup Bracket
Operating Temperature	-10°C to 40°C
Pan & Tilt Adjustment	80° (Pan Range 40° Left/Right From The Centre)

General

Weight (g)	91.5
Height (mm)	71
Width (mm)	130
Depth (mm)	127
Body Construction	Polycarbonate (Bracket 316 Stainless Steel, including screws)
Product Colour	Black
Accessories (Included)	Fittings

Data sheet

LEDXSSBRBN

Light / LED Wide Beam Lighting

EAN Number	5012483015018
Guarantee Period	3 Years

Line Diagrams

