

CONTACTUM



Make the switch

1 Gang 2 Way 400W Dimmer - Moulded, White

Stock code: ASP2614/2



Technical

Associated standards:	BS EN 60669-2
Ambient operating temperature:	-5 to 40°C (24hour average not exceeding 25°C)
Base material:	Thermoset
Face plate material:	thermoset
Fixing screws:	2 x M3.5
IP rating:	IP2X
Maximum installation altitude :	2000m
Minimum wall box depth :	35
Nature of supply:	AC
Operational testing :	10000
Rated frequency:	50-60Hz
Rated voltage:	220-250V
Rated watts :	400
Terminal capacity :	3 x 1.0mm 3 x 1.5mm 1 x 2.5mm

General

Actuator type:	Push ON-OFF
Dimmer type:	switch
Face plate finish:	moulded
Number of switches:	1
Switching operation:	2 way

Technical: +44 (0) 208 208 7414 **Sales:** +44 (0) 208 208 7419 **E-mail:** sales@contactum.co.uk