

PRODUCT-DETAILS

RF10711

INS NYL RING TERM, 4AN, 1/4, YELLOW



General Information

Extended Product Type	RF10711
Product ID	7TAI029860R0086
EAN	5414363160052
Catalog Description	INS NYL RING TERM, 4AN, 1/4, YELLOW
Long Description	Nylon Insulated Large Ring Terminal, Length 1.78 Inches, Width .55 Inches, Maximum Insulation .380, Bolt Hole 1/4 Inch, Wire Range 4AN, Color Yellow, Copper, Tin Plated

Ordering

EAN	5414363160052
UPC	786210830438

Dimensions

Product Net Length	0, mm
--------------------	-------

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	3.1 in 79 mm
Package Level 1 Height	4.69 in 119 mm

Package Level 1 Depth / Length	6.3 in 160 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	12.9 in 328 mm
Package Level 2 Height	3.8 in 97 mm
Package Level 2 Depth / Length	23.9 in 607 mm

Additional Information

Brand / Label	Sta-Kon
Color	Yellow
Effective Date	19680820
Material	Copper
Number of Batteries	0
Product Name	ELECTRICAL TERMINAL
Product Type	Nylon Insulated Ring Terminal
Special Functions	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standards	UL E9809
Voltage Rating	600 V
Wire Size	4AN

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	RF10711
Instructions and Manuals	RF10711

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

