

1434-4-6711

NOTES:

1. WIRE: U.L. LABELED TYPE SPT-1, #18 AWG, RATED 105°C, 300V. MAX., BLACK & CONFORMING TO U.L. STD 62.
2. MATERIAL: BLACK & U.L. RATED FOR 105°C. CONTINUOUS DUTY.
3. PLUG & CORD SETS TO MEET ALL APPLICABLE REQUIREMENTS OF U.L. STD'S 62, 498, & 817.
4. U.L. RATED 7A., 125V.
5. "L" LENGTH CAN BE DETERMINED BY DASH NUMBER FOLLOWING PART NUMBER. SEE ORDERING INFORMATION BELOW (NOTE 9).
6. TOLERANCE: "L" UP TO 48": $\begin{matrix} +2.0 \\ -0.0 \end{matrix}$
"L" OVER 48": $\begin{matrix} +3.0 \\ -0.0 \end{matrix}$
7. U.L. RECOGNIZED FILE E42397 & CSA CERTIFIED LR 45871.
8. ALL DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.
9. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS WILL HAVE A TOLERANCE OF ± 0.030 .

LENGTH "L" ebm PART NUMBER
24" 1434-4-6711

