

3293 U-3

Reversible ratchet 3/4"

Code	ETIM
6278790	EC002218
EAN	UNSPSC
4010886627877	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82041100	

Article description

- Particularly suitable for work in confined spaces
- Acc. to DIN 3122, ISO 3315
- With non-slip metal disc change, fine-toothed (72 teeth) and robust
- Return angle 5°
- With slip-on tube No. E-3293 U-3/90
- For hand-operated sockets and accessories with square drive as per DIN 3120 - D 20, ISO 1174 with locking pin
- Vanadium steel 31CrV3, chrome-plated

Article information

Contents (Qty of pieces)	1	Drive connector square (male)	20 mm
Net weight [kg]	2,61 kg	Return angle	5°
Total length [mm]	625 mm	Number of teeth	72
Total width [mm]	69 mm	Backup	Locking pin
Total height [mm]	64 mm	Ratchet head height	62,5 mm
Surface	chrome-plated	Locking type	Ball locking device
Material	Chrome-vanadium steel 31CrV3	Push button release	no
Standard	DIN 3122 ISO 3315	Shift type	Switching disk
Drive connector square (male)	3/4"		