



Technical data

HK5022L/3AS

Drawn cup needle roller bearings, opened end



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
Fw - Under rollers diameter	50 mm
D - External diameter	58 mm
C1 - Width of the drawn cup L	22 mm
C3 - Max drawn cup closed end thickness LL	2,7 mm
Lubrication hole on outer ring	Non/No
Inner ring reference	IR45X50X25
Mass	0,086 kg



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

HK5022L/3AS

Drawn cup needle roller bearings, opened end

PRODUCT PERFORMANCE

Cr - Dynamic load rating	31,5 kN
C0r - Static load rating	63 kN
N lim - Grease lubrication limit speed	3200 tr/min
Tmin - Min operating temperature	-20 °C
Tmax - Max operating temperature	100 °C

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	HK5022L/3AS
Image	NRBHK_L_1.jpg, NRBHK_L_3.jpg
Rolling element material	Acier 100Cr6



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15