

FEATURES

- A cost-effective and reliable solution
- Indicators on labels are in °C and °F
- A cost-effective and reliable solution
- Suitable for monitoring temperature over a certain period of time using 7 temperature increments

RS PRO Temperature Sensitive Label, 60°C to 90°C, 7 Levels

RS Stock No.: 286-175

| | | | | | | | | |
|----|-----|-----|-----|-----|-----|-----|-----|----|
| °C | 60 | 65 | 70 | 75 | 80 | 85 | 90 | °C |
| °F | 140 | 149 | 158 | 167 | 176 | 185 | 194 | °F |

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing the range of RS PRO temperature sensitive labels, ideal for use in the food, automotive, moulding and metal working industries. The labels have been designed as a temperature test strip that will make a permanent and irreversible record of the highest temperature bracket reached when applied to the surface of an object by changing colour. These heat-sensitive RS PRO temperature indication labels are a high quality and cost-effective solution that measures surface temperature accurately and provides reliable proof that the item or product has been maintained at the correct temperature and is suitable for use across a wide variety of applications

General Specifications

| | |
|-------------------------------------|--|
| Number of Temperature Levels | 7 |
| Orientation | Horizontal |
| Reversibility | Reversible |
| Scale | °C , °F |
| Shelf Life | 12 months |
| Adhesive Type | Double coated adhesive type |
| Colour Change Material | Non-toxic, mixture of liquid crystal esters |
| Tolerance | ±1°C |
| Covering Film | Polyester 5 mil stock |
| Storage | Store at room temperature |
| Pressure sensitive | No |
| Applications | Food Industry, Pharmaceuticals, Medical products, Industrial equipment, Shipping and packaging for sensitive goods |

Mechanical Specifications

| | |
|---------------------|---------------|
| Dimensions | 12.5mm X45 mm |
| Label Length | 12.5mm |
| Label Width | 45mm |

Operation Environment Specifications

| | |
|--|-------------|
| Minimum Temperature Sensitivity | 60°C |
| Maximum Temperature Sensitivity | 90°C |
| Storage Temperature | 21°C (70°F) |

Approvals

| | |
|----------------------------------|--------------------------------|
| Compliance/Certifications | RoHS Certificate of compliance |
|----------------------------------|--------------------------------|

Accessories

| Item Name | Item Description | Quantity |
|----------------------|--|-------------|
| Time indicator label | Time Strip Non reversible time indicator label , 19 x40mm 3 months | 1box of 100 |
| Time indicator label | Time Strip Non reversible time indicator label 19 x40mm 6 months | 1box of 100 |
| Time indicator label | Time Strip Non reversible time indicator label 19 x40mm 12months | 1box of 100 |
| Time indicator label | Time Strip Non reversible time indicator label 19 x40mm 1month | 1box of 100 |

