

30 JMU-10

Socket set 3/8"

16 pieces

Code
2682885

ETIM
EC002209

EAN
4010886934784

UNSPSC
27-11-17-03

Country of origin
Germany

eCl@ss
21-04-02-05

Customs tariff number
82042000



10 **3/8"** **mm**

Article description

- With forged, tempered hexagon (No. 30) or bi-hexagon (No. D 30) UD profile sockets, hand-operated
- With accessories made from GEDORE vanadium steel 31CrV3
- With robust lever-change reversible ratchet
- In GEDORE blue sheet steel case
- Dimensions: 320 x 132 x 55 mm

Article parts list

Ratchet, 3093 U-10, Inserts, 30 6 7 8 9 10, 11 12 13 14 15, 16 17 18 19, Accessories, 3/8" extension 3090-5

Article information

Contents (Qty of pieces)	16	Total height [mm]	55 mm
Net weight [kg]	2,2 kg	Total depth [mm]	132 mm
Total length [mm]	132 mm	Drive connector square female (metric)	10,0 mm
Total width [mm]	320 mm	Drive connector square female [inch]	3/8"