

Previously known as: Neptune® Kevlar®



Cut



Medium Duty

Kevlar®-lined protective arm sleeves, offering contact heat and cut resistance

- **Elevated comfort:** HyFlex® 70-123 protective sleeves feature an automatic knit liner, made with 100% Kevlar® para-aramid short fibers, resulting in superb wearer comfort
- **Advanced defenses:** The same Kevlar® para-aramid short fibers grant these arm protection sleeves advanced cut resistance capabilities, as well as contact heat protection up to 100°C/212°F
- **Enhanced features:** A convenient thumbslot ensures a secure fit and grants additional wrist protection



Industries

- Automotive
- Metal fabrication
- Machinery and Equipment

Applications

- Press shop operations
- Assembly & inspection of components
- Applying sealers, touching up
- Equipment repair & maintenance
- Cutting glasses, sheets, panels
- Seizing structural and body parts
- Adjusting systems and screwing

HyFlex®

ADVANCED MECHANICAL PROTECTION

70-123

Superior mechanical protection and cut-resistance

Previously known as: Neptune® Kevlar®

Key Features

- **Kevlar® para-aramid short fibers:** Cut resistance with superb comfort
- **Heat-resistant design:** Contact heat resistance up to 100°C/212°F
- **Thumbslot:** A secure fit with additional wrist protection

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	LENGTH	PACKAGE
HyFlex 70-123	Liner Material: Kevlar® Cuff Style: Knitwrist	10	22" (559 mm)	12 pieces/bag, 12 bags/carton

Technologies

Kevlar®

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell