

## Deep groove ball bearings 6304 (Series 63)

main dimensions to DIN 625-1

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

d	20 mm	
D	52 mm	
B	15 mm	
D <sub>1</sub>	41,9 mm	
d <sub>1</sub>	30,3 mm	
D <sub>a max</sub>	45 mm	
d <sub>a min</sub>	27 mm	
r <sub>a max</sub>	1,1 mm	
r <sub>min</sub>	1,1 mm	
m	0,151 kg	Mass
C <sub>r</sub>	16900 N	Basic dynamic load rating, radial

$C_{0r}$	7900 N	Basic static load rating, radial
$C_{ur}$	540 N	Fatigue limit load, radial
$n_G$	19800 1/min	Limiting speed
$n_{Gr}$	14400 1/min	Reference speed
$f_0$	12,4	Calculation factor



