

# Titan tweezers set 3 pcs

<b>Art.-No.</b>	5-030
<b>Description</b>	Titan tweezers set 3 pcs
<b>Application</b>	Electronics, SMD/THT assembly, precision mechanics, watchmakers, jewelers, medical technology.
<b>Specification</b>	Dimensions see data sheets individual articles (pictogram)
<b>Material</b>	Titan
<b>Surface/Coating</b>	matt finish
<b>Features</b>	antibacterial, antimagnetic, heat-resistant, solder-repellent:acid-resistant, stainless, seawater resistant
<b>Surface resistance</b>	/
<b>Total length</b>	measures 160 × 85 × 20 mm
<b>Weight</b>	weight 70 g

## Application and technical data

Tweezers are made entirely of TITAN (light metal) and meet the highest technical requirements. Melting point 1941 K (1668°C), thermal conductivity 22W, electrical conductivity  $2.5 \times 10^6$ .

Case consisting of ESD imitation leather, EPA suitable for electrostatically protected areas (ESD workplace/ESD protection zone corresponds to standard DIN EN 61340-5-1), dissipative  $10^6$  Ohm. The leatherette is flame retardant, biocompatible and contains a dissipative Velcro strap to prevent static charge when opening.

## Parts list

Titan tweezers set consists of:

- 5-030-0 ESD dissipative bag 3 empty pockets
- 5-031 titan tweezers 110 mm form 5
- 5-036 titan anatomical tweezers 145 mm form 40 serrated
- 5-037 titan anatomical tweezers 150 mm form 22b with guide pin serrated

