

## VARIO® LINEA connectable Overvoltage Protection optic 5-fold plus

For the connection of a individual supply

- ✓ Robust plastic, grey
- ✓ Built-in Schuko plug sockets (90° rotated), round
- ✓ Space of sockets: 64 mm
- ✓ Without supply
- ✓ Spacious connection chamber, cable entry (Ø 10 mm)
- ✓ Increased safety due to integrated child protection
- ✓ End caps: mounting possible

### Technical Data

- Voltage a<sub>c</sub> U<sub>c</sub>: 230 V~
- Rated current (-Power) 16 A (3600 W)
- Max. continuous operation voltage a<sub>c</sub> U<sub>c</sub>: 255 V~
- U<sub>oc</sub>: 5000 V
- Protection level Up: L-N < 1,0kV  
L/N-PE < 1,5kV
- I<sub>max</sub> (8/20) 6,5 kA
- Fuse: T6,3AH/250 V
- SPD according to EN 61643-11 Typ3
- Angle plug with earthing contact
- 2-pole, illuminated switch
- Consumption: < 0,5 W

Dimensions: 462 x 74 x 47 mm (L x W x H)  
EAN: 4012096029038  
Packaging unit: 10  
Article no.: 0205r10052300



**VARIO®**  
LINEA

Subject to technical changes.  
Special designs on request.

Review Date: 04/2013