

1550U

Pneumatic shock absorber removal tool

CE

Ideal for cars, SUVs and commercial vehicles.

Features

- Maximum thrust: 2 tons (10 bars) - 1.6 tons (8 bars) - 1.2 tons (6 bars)
- Spring compression stroke: 335 mm
- Upper universal hold system that allows all left/right-hand spring diameters to be compressed with one upper adaptable plate
- Active safety system on spring: safety hook and 3 locking valves allow spring to be properly positioned/seated, maintaining such position throughout compression
- If spring is not positioned properly, system will stop machine.
- Protective "Full Body" Grille: provides maximum safety and working area coverage
- Control Lever operation: increased accuracy and sensitivity during compression stage
- Working position: working height on rear fork raised up to 875 mm
- Supplied with 2 lower forks for diameters 78-205 mm

	art.	H	L	P
015500010	1550U	1670	825	610

